



WNE122B

cubyko Double horizontal socket 2P+E screwless flush mounted white IP55

Technical properties

Architecture

Type of pole 2P+T

Functions

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

Configuration

Number of modules 4

Compatibility

IFTTT support available No

Controls and indicators

Indicator lamp no

With or without indicator without

Connectivity

With USB charging socket No

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Depth of installed product 42.5 mm

Height of installed product 45 mm

Dimensions (LLxwwxhh) 83X83X43

Width of installed product 90 mm

Capacity

Number of modules for WA 4

Number of module locations 4

Cover, door

Lid shape hinge

Interlockable No

Power supply

Special power supply

No special power supply

Materials

RAL colour

RAL 9010 - Pure white

Material quality

Material mix

Surface appearance

satin finish

Transparent

No

Metallic colour

No

Installation, mounting

Fixing type

With screws

Mounting type

flush

Connection

Connection cross-sect. rigid cable

mini 2x1 mm² - maxi 2x2,5 mm²

Phase pickup

L1

Type of connection

Quickconnect

Accessories included

With miniature fuse

No

Equipment

Number of socket outlets switchable

0

On/Off switch

No

With transparent product label holder

No

Standards

Approvals

NFC 61314

Safety

IK protection code against mechanical impacts

07

REACH conform

Yes

RoHS conform

Yes

Halogen free

Yes

Protection

without protective screen

Use conditions

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Insulated

Yes

Identification

Range

cubyko