



WNE123

cubyko Triple horizontal socket 2P+E screwless flush mounted grey IP55

Technical properties

Architecture

Type of pole 2P+T

Functions

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

Configuration

Number of modules 6

Compatibility

IFTTT support available No

Controls and indicators

Indicator lamp no

With or without indicator without

Connectivity

With USB charging socket No

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 42.5 mm

Height of installed product 45 mm

Dimensions (LLxwwxhh) 83X83X44

Width of installed product 135 mm

Capacity

Number of modules for WA 6

Number of module locations 6

Cover, door

Lid shape hinge

Interlockable No

Power supply

Special power supply No special power supply

Materials

Material quality Material mix

Surface appearance satin finish

Transparent No

Metallic colour No

Installation, mounting

Fixing type With screws

Mounting type flush

Connection

Connection cross-sect. rigid cable mini 2x1 mm² - maxi 2x2,5 mm²

Phase pickup L1

Type of connection Quickconnect

Accessories included

With miniature fuse No

Equipment

Number of socket outlets switchable 0

On/Off switch No

With transparent product label holder No

Standards

Approvals NFC 61314

Safety

IK protection code against mechanical impacts 07

Protection without protective screen

Use conditions

Operating temperature -15...30 °C

Storage/transport temperature -50...50 °C

Insulated Yes

Identification

Range cubyyko