



WNE123B

**cubyko Triple horizontal socket 2P+E screwless flush mounted white IP55**

**Technical properties**

**Architecture**

Type of pole 2P+T

**Functions**

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

**Configuration**

Number of modules 6

**Compatibility**

IFTTT support available No

**Controls and indicators**

Indicator lamp no

With or without indicator without

**Connectivity**

With USB charging socket No

**Main electrical features**

Nominal voltage 250 V

Frequency 50/60 Hz

**Electric current**

Rated current 16 A

**Dimensions**

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 42.5 mm

Height of installed product 45 mm

Dimensions (LLxwwxhh) 83X83X45

Width of installed product 135 mm

**Capacity**

Number of modules for WA 6

Number of module locations 6

**Cover, door**

Lid shape hinge

Interlockable	No
<b>Power supply</b>	
Special power supply	No special power supply
<b>Materials</b>	
RAL colour	RAL 9010 - Pure white
Material quality	Material mix
Surface appearance	satin finish
Transparent	No
Metallic colour	No
<b>Installation, mounting</b>	
Fixing type	With screws
Mounting type	flush
<b>Connection</b>	
Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Phase pickup	L1
Type of connection	Quickconnect
<b>Accessories included</b>	
With miniature fuse	No
<b>Equipment</b>	
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No
<b>Standards</b>	
Approvals	NFC 61314
<b>Safety</b>	
IK protection code against mechanical impacts	07
Protection	without protective screen
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes
<b>Identification</b>	
Range	cubyko