



WNE123B

cubyko Triple horizontal socket 2P+E screwless flush mounted white IP55

Technical properties

Architecture

Fixing mode Screwed

Functions

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

Configuration

Number of modules 6

Compatibility

IFTTT support available No

Controls and indicators

Indicator lamp no

With or without indicator without

Connectivity

With USB charging socket No

Main electrical features

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 42.5 mm

Height of installed product 45 mm

Dimensions (LLxwwxhh) 83X83X45

Width of installed product 135 mm

Capacity

Number of modules for WA 6

Number of module locations 6

Cover, door

Lid shape hinge

Interlockable No

Power supply

Special power supply

No special power supply

Materials

RAL colour

RAL 9010 - Pure white

Transparent

No

Metallic colour

No

Connection

Type of connection

Quickconnect

Accessories included

With miniature fuse

No

Equipment

Number of socket outlets switchable

0

On/Off switch

No

With transparent product label holder

No

Safety

IK protection code against mechanical impacts

07

Use conditions

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Insulated

Yes

Identification

Range

cubyko