



WNE132

cubyko Double vertical socket 2P+E screwless flush mounted grey IP55

Technical properties

Architecture

Type of pole 2P+T

Functions

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

Configuration

Number of modules 4

Compatibility

IFTTT support available No

Controls and indicators

Indicator lamp no

With or without indicator without

Connectivity

With USB charging socket No

Main electrical features

Nominal voltage 250 V

Frequency 50/60 Hz

Electric current

Rated current 16 A

Dimensions

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 22.8 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 83X83X46

Width of installed product 75 mm

Capacity

Number of modules for WA 4

Number of module locations 4

Cover, door

Lid shape hinge

Interlockable	No
Power supply	
Special power supply	No special power supply
Materials	
Material quality	Material mix
Surface appearance	satin finish
Transparent	No
Metallic colour	No
Installation, mounting	
Fixing type	With screws
Mounting type	flush
Connection	
Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Phase pickup	L1
Type of connection	Quickconnect
Accessories included	
With miniature fuse	No
Equipment	
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No
Standards	
Approvals	NFC 61314
Safety	
IK protection code against mechanical impacts	07
Protection	without protective screen
Use conditions	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes
Identification	
Range	cubyko