



WNE132

**cubyko Double vertical socket 2P+E screwless flush mounted grey IP55**

**Technical properties**

**Architecture**

Fixing mode Screwed

**Functions**

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

**Configuration**

Number of modules 4

**Compatibility**

IFTTT support available No

**Controls and indicators**

Indicator lamp no

With or without indicator without

**Connectivity**

With USB charging socket No

**Main electrical features**

Frequency 50/60 Hz

**Electric current**

Rated current 16 A

**Dimensions**

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 22.8 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 83X83X46

Width of installed product 75 mm

**Capacity**

Number of modules for WA 4

Number of module locations 4

**Cover, door**

Lid shape hinge

Interlockable No

**Power supply**

Special power supply

No special power supply

**Materials**

RAL colour

RAL 7011 - Iron grey

Transparent

No

Metallic colour

No

**Connection**

Type of connection

Quickconnect

**Accessories included**

With miniature fuse

No

**Equipment**

Number of socket outlets switchable

0

On/Off switch

No

With transparent product label holder

No

**Safety**

IK protection code against mechanical impacts

07

**Use conditions**

Operating temperature

-15...30 °C

Storage/transport temperature

-50...50 °C

Insulated

Yes

**Identification**

Range

cubyko