



WNE132

**cubyko Double vertical socket 2P+E screwless flush mounted grey IP55**

**Technical properties**

**Architecture**

Type of pole 2P+T

**Functions**

Centralized terminal connections Yes

With orientation lighting No

Overvoltage protection No

**Configuration**

Number of modules 4

**Compatibility**

IFTTT support available No

**Controls and indicators**

Indicator lamp no

With or without indicator without

**Connectivity**

With USB charging socket No

**Main electrical features**

Nominal voltage 250 V

Frequency 50/60 Hz

**Electric current**

Rated current 16 A

**Dimensions**

Installation depth, flush-mounted boxes 40 mm

Depth of installed product 22.8 mm

Height of installed product 75 mm

Dimensions (LLxwwxhh) 83X83X46

Width of installed product 75 mm

**Capacity**

Number of modules for WA 4

Number of module locations 4

**Cover, door**

Lid shape hinge

Interlockable	No
---------------	----

---

**Power supply**

Special power supply	No special power supply
----------------------	-------------------------

---

**Materials**

Material quality	Material mix
Surface appearance	satin finish
Transparent	No
Metallic colour	No

---

**Installation, mounting**

Fixing type	With screws
Mounting type	flush

---

**Connection**

Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Phase pickup	L1
Type of connection	Quickconnect

---

**Accessories included**

With miniature fuse	No
---------------------	----

---

**Equipment**

Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No

---

**Standards**

Approvals	NFC 61314
-----------	-----------

---

**Safety**

IK protection code against mechanical impacts	07
Protection	without protective screen

---

**Use conditions**

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes

---

**Identification**

Range	cubyko
-------	--------