



WNE132B

cubyko Double vertical socket 2P+E screwless flush mounted white IP55

Technical properties

Architecture

Type of pole	2P+T
--------------	------

Functions

Centralized terminal connections	Yes
With orientation lighting	No
Overvoltage protection	No

Configuration

Number of modules	4
-------------------	---

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Indicator lamp	no
With or without indicator	without

Connectivity

With USB charging socket	No
--------------------------	----

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Dimensions

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	22.8 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	83X83X47
Width of installed product	75 mm

Capacity

Number of modules for WA	4
Number of module locations	4

Cover, door

Lid shape	hinge
-----------	-------

Interlockable	No
Power supply	
Special power supply	No special power supply
Materials	
RAL colour	RAL 9010 - Pure white
Material quality	Material mix
Surface appearance	satin finish
Transparent	No
Metallic colour	No
Installation, mounting	
Fixing type	With screws
Mounting type	flush
Connection	
Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Phase pickup	L1
Type of connection	Quickconnect
Accessories included	
With miniature fuse	No
Equipment	
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No
Standards	
Approvals	NFC 61314
Safety	
IK protection code against mechanical impacts	07
Protection	without protective screen
Use conditions	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes
Identification	
Range	cubyko