



WNE132B

**cubyko Double vertical socket 2P+E screwless flush mounted white IP55**

**Technical properties**

**Architecture**

Type of pole	2P+T
--------------	------

**Functions**

Centralized terminal connections	Yes
With orientation lighting	No
Overvoltage protection	No

**Configuration**

Number of modules	4
-------------------	---

**Compatibility**

IFTTT support available	No
-------------------------	----

**Controls and indicators**

Indicator lamp	no
With or without indicator	without

**Connectivity**

With USB charging socket	No
--------------------------	----

**Main electrical features**

Nominal voltage	250 V
Frequency	50/60 Hz

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	40 mm
Depth of installed product	22.8 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	83X83X47
Width of installed product	75 mm

**Capacity**

Number of modules for WA	4
Number of module locations	4

**Cover, door**

Lid shape	hinge
-----------	-------

Interlockable	No
<b>Power supply</b>	
Special power supply	No special power supply
<b>Materials</b>	
RAL colour	RAL 9010 - Pure white
Material quality	Material mix
Surface appearance	satin finish
Transparent	No
Metallic colour	No
<b>Installation, mounting</b>	
Fixing type	With screws
Mounting type	flush
<b>Connection</b>	
Connection cross-sect. rigid cable	mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup>
Phase pickup	L1
Type of connection	Quickconnect
<b>Accessories included</b>	
With miniature fuse	No
<b>Equipment</b>	
Number of socket outlets switchable	0
On/Off switch	No
With transparent product label holder	No
<b>Standards</b>	
Approvals	NFC 61314
<b>Safety</b>	
IK protection code against mechanical impacts	07
Protection	without protective screen
<b>Use conditions</b>	
Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	Yes
<b>Identification</b>	
Range	cubyko