



WUZ671



kallystx Ceiling loudspeaker

Technical properties

Functions

Loudness control	No
------------------	----

Dimensions

Insertion depth	62 mm
Installation opening Ø	116 mm
Recommended installation height	2.4...4 m
Installation wall thickness	30 mm
Loudspeaker chassis Ø	87 mm

Frequency

Frequency range audio	180 Hz...21 kHz
Frequency band	180 / 21000 Hz
Frequency response (-3 dB)	170...22000 Hz

Resistance

Impedance	8 Ω
-----------	-----

Detection

- at 1 kHz	180 °
- at 4 kHz	130 °
- at 8 kHz	80 °

Materials

Material	metal
----------	-------

Installation, mounting

Built-in	Yes
----------	-----

Connection

Conductor cross-section (flexible)	max. 2.5 mm ²
------------------------------------	--------------------------

Cable

Cable clamp	with strain relief
-------------	--------------------

Equipment

Sound pressure level 1 W/1 m	87 dB
Sound pressure level at rated power	95 dB

Identification

Main design line	Communication technology
------------------	--------------------------

