



WXA001

## Gallery Detrompeur

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Dimensions

Depth	23.7 mm
Height	35.9 mm
Width	31 mm

#### Materials

Material	Mixed materials
Surface appearance	matt/glossy
Type of surface treatment	untreated

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

European directive RoHs	voluntary compliance
European directive WEEE	not concerned

#### Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Composition	other
-------------	-------