



WXA001

Gallery Detrompeur

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	23.7 mm
Height	35.9 mm
Width	31 mm

Materials

Surface appearance	matt/glossy
Type of surface treatment	untreated

Connection

Type of contacts	2 way
------------------	-------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive RoHS	voluntary compliance
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	other