



WXA010

## Lamp gallery for plate 1P 230V pure-white

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Main electrical features

Nominal voltage	250 V
-----------------	-------

#### Electric current

Rated current	2.5 mA
---------------	--------

#### Dimensions

Depth	6.9 mm
-------	--------

Height	39.4 mm
--------	---------

Width	87.8 mm
-------	---------

#### Power

Current consumption	max. 2.5 mA
---------------------	-------------

#### Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

#### Lighting control

Light colour	white
--------------	-------

Type of lamp	LED
--------------	-----

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

Approvals	NF
-----------	----

European directive RoHs	voluntary compliance
-------------------------	----------------------

#### Safety

IK protection code against mechanical impacts	IK02
---	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

#### Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

#### Identification

Range

gallery

Composition

other