



WXA011

Lamp gallery for plate 1P 12/24V AC/DC pure-white

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Main electrical features

Nominal voltage	24 V
-----------------	------

Electric current

Rated current	7.5 mA
---------------	--------

Dimensions

Depth	6.9 mm
Height	39.4 mm
Width	87.8 mm

Power

Current consumption	max. 7.5 mA
---------------------	-------------

Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Lighting control

Light colour	white
Type of lamp	LED

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	NF
European directive RoHs	voluntary compliance

Safety

IK protection code against mechanical impacts	IK02
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range

gallery

Composition

other