



WXA011

Lamp gallery for plate 1P 12/24V AC/DC pure-white

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Main electrical features

Nominal voltage	24 V
-----------------	------

Electric current

Rated current	7.5 mA
---------------	--------

Dimensions

Depth	6.9 mm
-------	--------

Height	39.4 mm
--------	---------

Width	87.8 mm
-------	---------

Power

Current consumption	max. 7.5 mA
---------------------	-------------

Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Lighting control

Light colour	white
--------------	-------

Type of lamp	LED
--------------	-----

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	NF
-----------	----

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

IK protection code against mechanical impacts	IK02
-----------------------------------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range

gallery

Composition

other