



WXA011

Lamp gallery for plate 1P 12/24V pure-white

Technical properties

Architecture

Fixing mode Clipped

Main electrical features

Nominal voltage 24 V

Electric current

Rated current 7.5 mA

Dimensions

Depth 6.9 mm

Height 39.4 mm

Width 87.8 mm

Power

Current consumption max. 7.5 mA

Materials

Colour transparent

RAL colour RAL 9010 - Pure white

Lighting control

Light colour white

Type of lamp LED

Equipment

With transparent product label holder No

Standards

European directive RoHS voluntary compliance

European directive WEEE concerned

Safety

IK protection code against mechanical impacts IK02

Protection index IP IP20

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range

gallery

Composition

other