



WXA012

## Lamp gallery for plate 2P 230V pure-white

### Technical properties

#### Architecture

Fixing mode Clipped

#### Main electrical features

Nominal voltage 24 V

#### Electric current

Rated current 2.5 mA

#### Dimensions

Depth 6.9 mm

Height 39.4 mm

Width 158.7 mm

#### Power

Current consumption max. 2.5 mA

#### Materials

Colour white

RAL colour RAL 9010 - Pure white

#### Lighting control

Light colour white

Type of lamp LED

#### Equipment

With transparent product label holder No

#### Standards

European directive RoHs voluntary compliance

European directive WEEE concerned

#### Safety

IK protection code against mechanical impacts IK02

Protection index IP IP20

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range

gallery

Composition

other