



WXA450

## Frame gallery 2 modules

### Technical properties

#### Architecture

Fixing mode	Screwed
-------------	---------

#### Dimensions

Depth	8.7 mm
Height	73.8 mm
Width	73.8 mm

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Surface appearance	matt
Type of surface treatment	untreated

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

IK protection code against mechanical impacts	05
---	----

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range	gallery
Composition	basis element