



WXA451

## Frame gallery 1 module

### Technical properties

#### Architecture

|             |         |
|-------------|---------|
| Fixing mode | Screwed |
|-------------|---------|

#### Dimensions

|        |         |
|--------|---------|
| Depth  | 7.5 mm  |
| Height | 75 mm   |
| Width  | 33.5 mm |

#### Capacity

|                   |   |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

#### Materials

|                           |                      |
|---------------------------|----------------------|
| Colour                    | dark grey            |
| RAL colour                | RAL 7011 - Iron grey |
| Surface appearance        | matt                 |
| Type of surface treatment | untreated            |

#### Equipment

|                                       |    |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

#### Standards

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

#### Safety

|   |    |
|---|----|
| IK protection code against mechanical impacts | 05 |
|---|----|

#### Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

#### Identification

|             |               |
|-------------|---------------|
| Range       | gallery       |
| Composition | basis element |