



WXA454

### Frame gallery 4 modules entr. 57mm

#### Technical properties

##### Dimensions

Depth	8.5 mm
Height	73.8 mm
Width	130.8 mm

##### Capacity

Number of sockets	1
-------------------	---

##### Materials

Surface appearance	matt
Type of surface treatment	untreated

##### Equipment

With transparent product label holder	No
---------------------------------------	----

##### Standards

Approvals	NF
European directive WEEE	not concerned

##### Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes

##### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

##### Identification

Range	gallery
Composition	basis element