



WXA454

Frame gallery 4 modules entr. 57mm

Technical properties

Architecture

Fixing mode Screwed

Dimensions

Depth 8.5 mm

Height 73.8 mm

Width 130.8 mm

Capacity

Number of sockets 1

Materials

Colour dark grey

RAL colour RAL 7011 - Iron grey

Surface appearance matt

Type of surface treatment untreated

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition basis element