



WXA456

**Frame gallery 6 modules entr. 57mm**

**Technical properties**

**Dimensions**

Depth	8.5 mm
Height	73.8 mm
Width	187.8 mm

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Surface appearance	matt
Type of surface treatment	untreated

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

Approvals	NF
European directive WEEE	not concerned

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Range	gallery
Composition	basis element