



WXA458

Frame gallery 8 modules entr. 71mm

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Dimensions

Depth	8.5 mm
-------	--------

Height	73.8 mm
--------	---------

Width	215.8 mm
-------	----------

Capacity

Number of sockets	1
-------------------	---

Materials

Colour	dark grey
--------	-----------

RAL colour	RAL 7011 - Iron grey
------------	----------------------

Surface appearance	matt
--------------------	------

Type of surface treatment	untreated
---------------------------	-----------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
---	----

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------

Composition	basis element
-------------	---------------