



WXA458

## Frame gallery 8 modules entr. 71mm

### Technical properties

#### Dimensions

Depth	8.5 mm
Height	73.8 mm
Width	215.8 mm

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Surface appearance	matt
Type of surface treatment	untreated

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

Approvals	NF
European directive WEEE	not concerned

#### Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

#### Identification

Range	gallery
Composition	basis element