



WXA458

Frame gallery 8 modules entr. 71mm

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Dimensions

Depth	8.5 mm
Height	73.8 mm
Width	215.8 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Colour	dark grey
RAL colour	RAL 7011 - Iron grey
Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	untreated

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

Approvals	NF
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Composition	basis element
-------------	---------------