



WXA462B

## Frame gallery 2 modules Kallysta plate pure-white

### Technical properties

#### Architecture

Fixing mode Screwed

#### Dimensions

Depth 19.4 mm

Height 75 mm

Width 75 mm

#### Capacity

Number of sockets 1

#### Materials

Free area for finishing name pure

Colour white

Type of surface treatment Nickel-plated

#### Standards

European directive WEEE not concerned

#### Safety

IK protection code against mechanical impacts IK02

Protection index IP IP20

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition basis element