



WXA462D

Frame gallery 2 modules Kallysta plate dune

Technical properties

Dimensions

Depth	19.4 mm
Height	75 mm
Width	75 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	dune
Surface appearance	glossy

Standards

Approvals	NF
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	IK02
---	------

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	basis element