



WXA462D

Frame gallery 2 modules Kallysta plate dune

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Dimensions

Depth	19.4 mm
Height	75 mm
Width	75 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	dune
RAL colour	RAL 1013 - Oyster white
Type of surface treatment	Nickel-plated

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	basis element