



WXA681B

Wall box gallery single pure-white

Technical properties

Architecture

Fixing mode surface-mounting

Dimensions

Depth 45.3 mm

Height 90.8 mm

Width 94.8 mm

Materials

Free area for finishing name pure

Colour white

Type of surface treatment untreated

Installation, mounting

Mounting way vertical and horizontal

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted housing