



WXA683N

Wall box gallery triple night

Technical properties

Dimensions

Depth	45.3 mm
Height	90.8 mm
Width	236.8 mm

Materials

Free area for finishing name	night
Surface appearance	satin finish

Installation, mounting

Mounting way	horizontal
--------------	------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	Surface mounted housing