



WXA686B

## Wall box gallery 16 modules pure-white

### Technical properties

#### Architecture

Fixing mode surface-mounting

#### Dimensions

Depth 50.3 mm

Height 167.1 mm

Width 238.1 mm

#### Materials

Free area for finishing name pure

Colour white

Type of surface treatment untreated

#### Installation, mounting

Mounting way horizontal

#### Standards

European directive WEEE not concerned

#### Safety

IK protection code against mechanical impacts 05

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition Surface mounted housing