



WXA686T

Wall box gallery 16 modules Titane

Technical properties

Architecture

Fixing mode surface-mounting

Dimensions

Depth 50.3 mm

Height 167.1 mm

Width 238.1 mm

Materials

Free area for finishing name titane

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Installation, mounting

Mounting way horizontal

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted housing