



WXA690

## Lamp for switch gallery 230V blue

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Main electrical features

Nominal voltage	250 V
-----------------	-------

#### Electric current

Rated current	0.5 mA
---------------	--------

#### Dimensions

Depth	17.55 mm
Height	17.1 mm
Width	17.1 mm

#### Power

Current consumption	max. 0.5 mA
---------------------	-------------

#### Materials

RAL colour	RAL 9010 - Pure white
Material	Polycarbonate (PC)

#### Lighting control

Type of lamp	LED
--------------	-----

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

Approvals	NF
European directive RoHs	voluntary compliance
European directive WEEE	concerned

#### Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C