



WXA692

Lamp for switch gallery 230V white

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

Electric current

| | |
|---------------|--------|
| Rated current | 0.5 mA |
|---------------|--------|

Dimensions

| | |
|-------|----------|
| Depth | 17.55 mm |
|-------|----------|

| | |
|--------|---------|
| Height | 17.1 mm |
|--------|---------|

| | |
|-------|---------|
| Width | 17.1 mm |
|-------|---------|

Power

| | |
|---------------------|-------------|
| Current consumption | max. 0.5 mA |
|---------------------|-------------|

Materials

| | |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
|------------|-----------------------|

Lighting control

| | |
|--------------|-----|
| Type of lamp | LED |
|--------------|-----|

Standards

| | |
|-----------|----|
| Approvals | NF |
|-----------|----|

| | |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
|-------------------------|----------------------|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | IK02 |
|---|------|

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...35 °C |
|-----------------------|-------------|

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -10...50 °C |
|-------------------------------|-------------|

Identification

| | |
|-------|---------|
| Range | gallery |
|-------|---------|

| | |
|-------------|-------|
| Composition | other |
|-------------|-------|