



WXA693

Lamp for switch gallery 230V green

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Main electrical features

Nominal voltage	250 V
-----------------	-------

Electric current

Rated current	0.5 mA
---------------	--------

Dimensions

Depth	17.55 mm
Height	17.1 mm
Width	17.1 mm

Power

Current consumption	max. 0.5 mA
---------------------	-------------

Materials

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Lighting control

Type of lamp	LED
--------------	-----

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive RoHS	voluntary compliance
European directive WEEE	concerned

Safety

IK protection code against mechanical impacts	IK02
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

