



WXD000B

**Rocker switch gallery 2 modules pure-white**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Dimensions**

Depth 8 mm

Height 44.6 mm

Width 44.7 mm

**Capacity**

Number of sockets 1

**Materials**

Colour white

Surface appearance glossy

Type of surface treatment untreated

**Equipment**

With transparent product label holder No

**Standards**

European directive WEEE not concerned

**Safety**

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

**Identification**

Range gallery

Composition other