



WXD000N

Rocker switch gallery 2 modules night

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	8 mm
-------	------

Height	44.6 mm
--------	---------

Width	44.7 mm
-------	---------

Capacity

Number of sockets	1
-------------------	---

Materials

Surface appearance	satın finish
--------------------	--------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
---	----

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------

Composition	other
-------------	-------