



WXD000T

Rocker switch gallery 2 modules titane

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 8 mm

Height 44.6 mm

Width 44.7 mm

Capacity

Number of sockets 1

Materials

Surface appearance satin finish

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition other