



WXD002D

Rocker for switch gallery with FPL 2 modules dune

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	8 mm
Height	44.6 mm
Width	44.7 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Surface appearance	glossy
Type of surface treatment	untreated

Equipment

With transparent product label holder	Yes
---------------------------------------	-----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	other