



WXD003D

**Rocker VMC gallery 2 modules dune**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Dimensions**

Depth	8 mm
Height	44.6 mm
Width	44.7 mm

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Surface appearance	glossy
Type of surface treatment	untreated

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Range	gallery
Composition	other