



WXD003N

Rocker VMC gallery 2 modules night

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 8 mm

Height 44.6 mm

Width 44.7 mm

Capacity

Number of sockets 1

Materials

Colour deep black

RAL colour RAL 9005 - Jet black

Type of surface treatment Painted

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition other