



WXD005T

Rocker for switch gallery pull cord titane

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Dimensions

| | |
|-------|-------|
| Depth | 17 mm |
|-------|-------|

| | |
|--------|-------|
| Height | 45 mm |
|--------|-------|

| | |
|-------|-------|
| Width | 45 mm |
|-------|-------|

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|------------------------------|--------|
| Free area for finishing name | titane |
|------------------------------|--------|

| | |
|--------------------|--------------|
| Surface appearance | satın finish |
|--------------------|--------------|

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 05 |
|---|----|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...35 °C |
|-----------------------|-------------|

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -10...50 °C |
|-------------------------------|-------------|

Identification

| | |
|-------|---------|
| Range | gallery |
|-------|---------|

| | |
|-------------|-------|
| Composition | other |
|-------------|-------|