



WXD011D

Rocker with light indicator switch gallery 1 module dune

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	7.4 mm
Height	44.6 mm
Width	22.2 mm

Materials

Surface appearance	glossy
Type of surface treatment	untreated

Equipment

Monitoring window/light outlet	Yes
With transparent product label holder	No

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	other