



WXD011D

Rocker with light indicator switch gallery 1 module dune

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 7.4 mm

Height 44.6 mm

Width 22.2 mm

Materials

RAL colour RAL 1013 - Oyster white

Type of surface treatment untreated

Equipment

Monitoring window/light outlet Yes

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition other