



WXD011H

Rocker with light indicator switch gallery 1 module pure-white

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 7.4 mm

Height 44.6 mm

Width 22.2 mm

Materials

Colour white

Surface appearance glossy

Type of surface treatment untreated

Equipment

Monitoring window/light outlet Yes

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition other