



WXD012D

Rocker for switch gallery with FPL 1 module dune

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 7.4 mm

Height 44.6 mm

Width 22.2 mm

Materials

Surface appearance glossy

Type of surface treatment untreated

Equipment

With transparent product label holder Yes

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Halogen free Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition other