



WXD103H

Rocker for socket 2P+E gallery with light pure-white

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Dimensions

| | |
|--------|---------|
| Depth | 17.2 mm |
| Height | 45 mm |
| Width | 45 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|------------------------------|---------------|
| Free area for finishing name | antibactérien |
| Colour | white |
| Surface appearance | glossy |
| Type of surface treatment | untreated |

Equipment

| | |
|---------------------------------------|-----|
| Monitoring window/light outlet | Yes |
| With transparent product label holder | No |

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---|-----|
| IK protection code against mechanical impacts | 05 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|-------------|---------|
| Range | gallery |
| Composition | other |