



WXD155D

Rocker cable outlet gallery dune

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 24 mm

Height 45 mm

Width 45 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name dune

Surface appearance glossy

Type of surface treatment untreated

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition other

With imprint No