



WXD201D

Rocker for RJ45 socket gallery 1 module dune

Technical properties

Architecture

| | |
|-------------|--------------|
| Type | Modular Jack |
| Fixing mode | Clipped |

Connectivity

| | |
|--------|----------------------|
| Outlet | with straight outlet |
|--------|----------------------|

Dimensions

| | |
|--------|---------|
| Depth | 8.4 mm |
| Height | 45 mm |
| Width | 22.5 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 1 |
|-------------------|---|

Materials

| | |
|------------------------------|-------------------------|
| Free area for finishing name | dune |
| RAL colour | RAL 1013 - Oyster white |
| Type of surface treatment | untreated |

Equipment

| | |
|------------------------------------|-------------------------|
| Supporting plate / Supporting ring | without supporting ring |
|------------------------------------|-------------------------|

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 05 |
|---|----|

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|--------------------|--------------------------|
| Application, usage | Communication technology |
| Range | gallery |
| Composition | other |
| With imprint | No |