



WXD201H

Rocker for RJ45 socket gallery 1 module pure-white

Technical properties

Architecture

Type	Modular Jack
Fixing mode	Clipped

Connectivity

Outlet	with straight outlet
--------	----------------------

Dimensions

Depth	8.4 mm
Height	45 mm
Width	22.5 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	antibactérien
Colour	white
Surface appearance	glossy
Type of surface treatment	untreated

Equipment

Supporting plate / Supporting ring	without supporting ring
------------------------------------	-------------------------

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Application, usage	Communication technology
Range	gallery

Composition

other

With imprint

No